



Dynalite Multipurpose Controllers

DMC4-CE

Within any project, many different lighting load types may be required to achieve a desired result. Each of these load types may require a different style of control. The Philips Dynalite range of multipurpose controllers allows customization of output types via different output module units. When using DIN-rail multipurpose controllers, a specific type of control can be chosen for each circuit: relay, leading-edge dimmer, trailing-edge dimmer, ballast control, controller with out-of-the-box functionality, fan control, and blind/screen control. In any combination, multiple load types can be controlled from a single device. This simplifies installation and prevents wasted capacity of circuits that are not required.

Product data

General Information		Full product name	DMC4-CE
Remarks	Please download the Lighting – Product Data Sheet for more information and ordering options	Full EOC	871869688658800
CE mark	CE mark	Order code	88658800
EU RoHS compliant	Yes	Material no. (12 NC)	913703667909
Temperature		SAP numerator – quantity per pack	1
Ambient temperature range	0 to +40 °C	EAN/UPC – Product/Case	8718696886588
Product Data		Numerator – packs per outer box	1
Order product name	DMC4-CE	EAN/UPC – Case	8718696893586

Dynalite Multipurpose Controllers

Dimensional drawing

