



Dynalite Multipurpose Controllers

DMR610GL-CE

Within any project, many different lighting load types may be required to achieve a desired result. Each of these load types may require a different style of control. The Philips Dynalite range of multipurpose controllers allows customization of output types via different output module units. When using DIN-rail multipurpose controllers, a specific type of control can be chosen for each circuit: relay, leading-edge dimmer, trailing-edge dimmer, ballast control, controller with out-of-the-box functionality, fan control, and blind/screen control. In any combination, multiple load types can be controlled from a single device. This simplifies installation and prevents wasted capacity of circuits that are not required.

Product data

General Information		Full product name	DMR610GL-CE
Remarks	Please download the Lighting – Product Data Sheet for more information and ordering options	Full EOC	871869688661800
CE mark	CE mark	Order code	88661800
EU RoHS compliant	Yes	Material no. (12 NC)	913703668209
Temperature		SAP numerator – quantity per pack	1
Ambient temperature range	0 to +40 °C	EAN/UPC – Product/Case	8718696886618
Product Data		Numerator – packs per outer box	1
Order product name	DMR610GL-CE	EAN/UPC – Case	8718696893616

Dynalite Multipurpose Controllers

Dimensional drawing

