



Electronic parallel ignitor for HID lamp circuits

SI 51 Plus

HID ignitors for parallel systems


Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Wiring	
Connector Type	Screw
Temperature	
Ambient temperature range	-20 °C to 75 °C
T-Case Maximum (Max)	80 °C
Mechanical and Housing	
Housing	Akulon S223

Approval and Application	
Approval Marks	CE marking ENEC certificate
Product Data	
Order product name	SI 51 Plus
Full product name	SI 51 Plus
Full product code	697013372887100
Order code	913710011113
Material Nr. (12NC)	913710011113
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6970133728871
Numerator - Packs per outer box	48
EAN/UPC - Case	6970133728888

Electronic parallel ignitor for HID lamp circuits

Dimensional drawing



Product	C1	A1	A2	B1	D1
SI 51 Plus	38.5 mm	85.5 mm	65.0 mm	41.5 mm	4.3 mm

