



Electronic digital control ignitor for HID lamp circuits

SU 42-S

HID ignitors for series systems


Product data

Operating and Electrical	
Input Voltage	220 to 230 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Wiring	
Connector Type	Screw
Temperature	
T-Case Maximum (Max)	105 °C
Mechanical and Housing	
Housing	PC UL94V-2
Approval and Application	
Approval Marks	CE marking China Quality Certificate CB Certificate

Product Data	
Order product name	SU 42-S
Full product name	SU 42-S
Full product code	697013372897000
Order code	913710016213
Material Nr. (12NC)	913710016213
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6970133728970
Numerator - Packs per outer box	20
EAN/UPC - Case	6970133728987

Electronic digital control ignitor for HID lamp circuits

Dimensional drawing



Product	A2	C1	A1	B1
SU 42-S	63.4 mm	34 mm	96 mm	45 mm

