



# Electronic digital control ignitor for HID lamp circuits

## SU 42-S

HID ignitors for series systems


### Product data

General Information	
Application Code	42-S
Operating and Electrical	
Input Voltage	220 to 230 V
Input Frequency	50 to 60 Hz
Igniton Type	Series
Response Voltage	198 V
Mains Voltage Performance (AC)	-8% - +6%
Mains Voltage Safety (AC)	-10% - +10%
Power Losses (Nom)	3 W
Wiring	
Ballast Contact Wire Cross Section	0.50-2.50 mm <sup>2</sup>
Connector Type	Screw
Temperature	
T-Ambient (Nom)	75 °C
T-Case Maximum (Max)	105 °C

Mechanical and Housing	
Housing	PC UL94V-2
Approval and Application	
Approval Marks	CE marking China Quality Certificate CB Certificate
Product Data	
Full product code	697013372897000
Order product name	SU 42-S
EAN/UPC - Product	6970133728970
Order code	913710016213
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	913710016213
Net Weight (Piece)	0.200 kg

## Electronic digital control ignitor for HID lamp circuits

### Dimensional drawing



Product	A2	C1	A1	B1
SU 42-S	63.4 mm	34 mm	96 mm	45 mm

SU 42-S

