




Electronic transformers

ET-E 10 220-240V

A high frequency electronic transformer for operation with 12V halogen lamps. It is fully IEC compliant with unique compact size and light weight

Warnings and Safety

- Transformer is not suitable for DC operation
- Transformer is not suitable for DC operation


Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Inrush Current Width	0.10 ms
Inrush Current Peak (Max)	15 A
Wiring	
Cable Length From Device to Lamp	1.5 m
Temperature	
Ambient temperature range	-20 °C to 50 °C
T-Case Maximum (Max)	65 °C

Product Data	
Order product name	ET-E 10 220-240V
Full product name	ET-E 10 220-240V
Full product code	697013372907600
Order code	913710032179
Material Nr. (12NC)	913710032179
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6970133729076
Numerator - Packs per outer box	48
EAN/UPC - Case	6970133729083

Electronic transformers

Dimensional drawing



Product	D1	C1	A1	B1
ET-E 10 220-240V	4.4 mm	24.5 mm	76.0 mm	38.0 mm

