

LED Transformer for LED strip

LED Transformer 60W 24VDC

Constant voltage LED transformer for 24VDC LED application, compatible with Philips and other LED strip and offer 24VDC interface to LED application


Product data

| Operating and Electrical | |
|--|---------------|
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 to 60 Hz |
| Input frequency | 50 to 60 Hz |
| Inrush current width | 0.33 ms |
| Inrush current peak (max.) | 28 A |
| Number of products on MCB (16 A type B) (max.) | 13 |
| Wiring | |
| Connector type input terminals | Screw |
| Colour input terminals | Green |
| Colour output terminals | Green |
| Connector type output terminals | Screw |
| Cable length from device to lamp | 1.0 m |
| Temperature | |
| Ambient temperature range | -20°C to 50°C |

| T-Case maximum (max.) | 85 °C |
|-----------------------------------|---|
| Approval and Application | |
| Approval marks | CE marking RoHS compliant CCC certificate SELV ENEC certificate |
| Product Data | |
| Order product name | LED Transformer 60W 24VDC |
| Full product name | LED Transformer 60W 24VDC |
| Full EOC | 697013372909000 |
| Order code | 72909000 |
| Material no. (12 NC) | 913710032267 |
| SAP numerator – quantity per pack | 1 |
| EAN/UPC – Product/Case | 6970133729090 |
| Numerator – packs per outer box | 20 |
| EAN/UPC - Case | 6970133729106 |

LED Transformer for LED strip

Dimensional drawing



| Product | A1 | A2 | B1 | B2 | C1 |
|---------------------------|--------|--------|-------|---------|-------|
| LED Transformer 60W 24VDC | 180 mm | 170 mm | 52 mm | 42.0 mm | 30 mm |

