



# LED Transformer for LED strip

## LED Transformer 120W 24VDC

Constant voltage LED transformer for 24VDC LED application, compatible with Philips and other LED strip and offer 24VDC interface to LED application

### Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Inrush current width	0.32 ms
Inrush current peak (max.)	35 A
Number of products on MCB (16 A type B) (max.)	12

  

Wiring	
Connector type input terminals	Screw
Connector type output terminals	Screw
Cable length from device to lamp	1.0 m

  

Temperature	
Ambient temperature range	-20°C to 50°C
T case lifetime (max.)	65 °C
T-Case maximum (max.)	90 °C

Approval and Application	
Approval marks	CE marking RoHS compliant CCC certificate SELV ENEC certificate

  

Product Data	
Order product name	LED Transformer 120W 24VDC
Full product name	LED Transformer 120W 24VDC
Full EOC	694793910202000
Order code	10202000
Material no. (12 NC)	913710032567
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	6947939102020
Numerator – packs per outer box	20
EAN/UPC - Case	6947939102037

## LED Transformer for LED strip

### Dimensional drawing

Product	A1	A2	B1	B2	C1
LED Transformer 120W 24VDC	300 mm	290 mm	40 mm	29 mm	30 mm

