

Electronic transformers

ET-E 30 220-240V

A high frequency electronic transformer for operation with 12V halogen lamps. It is fully IEC compliant with unique compact size and light weight

Warnings and Safety

- Transformer is not suitable for DC operation

Product data

| Operating and Electrical | |
|----------------------------------------------|--------------|
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 to 60 Hz |
| Input Frequency | 50 to 60 Hz |
| Inrush Current Width | 0.28 ms |
| Inrush Current Peak (Max) | 10 A |
| Number of Products on MCB (16A Type B) (Max) | 50 |

| Wiring | |
|----------------------------------|-----------------|
| Connector Type Input Terminals | cable |
| Color Input Terminals | Black and White |
| Color Output Terminals | Red |
| Connector Type Output Terminals | cable |
| Cable Length From Device to Lamp | 1.5 m |

| Temperature | |
|---------------------------|-----------------|
| Ambient temperature range | -20 °C to 50 °C |


| | |
|----------------------|-------|
| T-Case Maximum (Max) | 65 °C |
|----------------------|-------|

| Approval and Application | |
|--------------------------|------|
| Approval Marks | SELV |

| Product Data | |
|---------------------------------|------------------|
| Order product name | ET-E 30 220-240V |
| Full product name | ET-E 30 220-240V |
| Full product code | 694793917165100 |
| Order code | 913710032964 |
| Material Nr. (12NC) | 913710032964 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 6947939171651 |
| Numerator - Packs per outer box | 48 |
| EAN/UPC - Case | 6947939171668 |

Electronic transformers

Dimensional drawing



| Product | D1 | C1 | A1 | B1 | A2 |
|------------------|--------|---------|-------|-------|-------|
| ET-E 30 220-240V | 4.4 mm | 24.5 mm | 76 mm | 38 mm | 72 mm |

