

Electronic transformers

ET-E 30 220-240V

A high frequency electronic transformer for operation with 12V halogen lamps. It is fully IEC compliant with unique compact size and light weight

Warnings and Safety

- Transformer is not suitable for DC operation


Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Inrush Current Width	0.28 ms
Inrush Current Peak (Max)	10 A
Number of Products on MCB (16A Type B) (Max)	50
Wiring	
Connector Type Input Terminals	cable
Color Input Terminals	Black and White
Color Output Terminals	Red
Connector Type Output Terminals	cable
Cable Length From Device to Lamp	1.5 m
Temperature	
Ambient temperature range	-20 °C to 50 °C

T-Case Maximum (Max)	65 °C
Approval and Application	
Approval Marks	SELV
Product Data	
Full product code	694793917165100
Order product name	ET-E 30 220-240V
Order code	913710032964
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	48
Material Nr. (12NC)	913710032964
Full product name	ET-E 30 220-240V
EAN/UPC - Case	6947939171668
EAN/UPC - Product/Case	6947939171651

Electronic transformers

Dimensional drawing



Product	D1	C1	A1	B1	A2
ET-E 30 220-240V	4.4 mm	24.5 mm	76 mm	38 mm	72 mm

