
PHILIPS

Lighting



HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 250L 301I TS

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Input Frequency	50 Hz


Wiring	
Connector Type	Screw

Product Data	
Order product name	BSN 250L 301I TS

Full product name	BSN 250L 301I TS
Full product code	871016303120030
Order code	913710102143
Material Nr. (12NC)	913710102143
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163148281
Numerator - Packs per outer box	6
EAN/UPC - Case	8710163032191

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 250L 301I TS	6.3 mm	64.5 mm	150.0 mm	135.0 mm	72.5 mm

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.