

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 400L 301I

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.


Product data

Operating and Electrical	
Input Voltage	220 V
Line Frequency	60 Hz
Input Frequency	60 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking
Product Data	
Order product name	BSN 400L 301I

Full product name	BSN 400L 301I
Full product code	871016303473730
Order code	913710102950
Material Nr. (12NC)	913710102950
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163148830
Numerator - Packs per outer box	4
EAN/UPC - Case	8710163034836

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 400L 301I	6.2 mm	82 mm	165.0 mm	150 mm	96.5 mm

