



# HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

## BSN 100L 300I

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

### Product data

<b>Operating and Electrical</b>		<b>Full product name</b>	
Input Voltage	220 V	Full product code	BSN 100L 300I
Line Frequency	50 Hz	Order code	871016303151430
Input Frequency	50 Hz	Material Nr. (12NC)	913710103750
<b>Wiring</b>		Numerator - Quantity Per Pack	1
Connector Type	Screw	EAN/UPC - Product/Case	8710163031514
<b>Approval and Application</b>		Numerator - Packs per outer box	6
Approval Marks	CE marking	EAN/UPC - Case	8710163032504
<b>Product Data</b>			
Order product name	BSN 100L 300I		

# HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

## Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 100L 300I	6.2 mm	51.5 mm	122.0 mm	107 mm	57.1 mm

