



HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 70L 301I


The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

Operating and Electrical		Full product name	BSN 70L 301I
Input Voltage	220 V	Full product code	871016303162030
Line Frequency	60 Hz	Order code	913710104643
Input Frequency	60 Hz	Material Nr. (12NC)	913710104643
Wiring		Numerator - Quantity Per Pack	1
Connector Type	Screw	EAN/UPC - Product/Case	8710163148519
Approval and Application		Numerator - Packs per outer box	6
Approval Marks	CE marking	EAN/UPC - Case	8710163032610
Product Data			
Order product name	BSN 70L 301I		

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 70L 301I	6.2 mm	51.5 mm	117.0 mm	102 mm	57.1 mm

