



BASIC

EB 2X20W TL-T 127-220V 50/60Hz HPF

Text only available in Brazilian



Product data

Operating and Electrical	
Input Voltage	127-220 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Wiring	
Connector Type Input Terminals	N/A
Connector Type Output Terminals	N/A
Cable Length From Device to Lamp	2 m
Input Wire Cross Section (Nom)	0.5 mm ²
Temperature	
Ambient temperature range	10 °C to 50 °C
T-Case Maximum (Max)	65 °C
Approval and Application	
Safety Standard	NBR14417

Environmental Standard	-
Product Data	
Full product code	871829173729200
Order product name	EB 2X20W TL-T 127-220V 50/60Hz HPF
Order code	913711126201
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	913711126201
Full product name	EB 2X20W TL-T 127-220V 50/60Hz HPF
EAN/UPC - Case	7894400004743
EAN/UPC - Product/Case	7894400002190

BASIC

Dimensional drawing



Product	C1	A2	D1	A1	B1
EB 2X20W TL-T 127-220V 50/60Hz HPF	35.0 mm	123.0 inch	5.0 inch	132.0 mm	48.0 mm

