



HID-Basic ballasts for HPL and HPI(PLUS) lamps

BHLE 250L 200 TS

The HID-Basic ballast is an impregnated (HID standard) electromagnetic ballast for HID lamps, for use in combination with an external ignitor.


Product data

General Information	
Application Code	L200 TS
Operating and Electrical	
Input Voltage	220 V
Input Frequency	50 Hz
Power Factor 100% Load (Min)	0.85
Mains Voltage Performance (AC)	-8%+6%
Mains Voltage Safety (AC)	-10%+10%
Input Current with PF Correction	1.35 A
Input Current without PF Correction	2.13/2.15 A
Power Factor without PF Compensation (Nom)	0.60
Power Losses (Nom)	20 W
Wiring	
Connector Type	Screw
System characteristics	
Rated Ballast-Lamp Power	250 W

Temperature	
T-Winding (Max)	130 °C
Delta-T Normal Conditions	70/75 °C
Approval and Application	
Approval Marks	CE marking
Product Data	
Full product code	694818229900000
Order product name	BHLE 250L 200 TS
EAN/UPC - Product	6948182295842
Order code	913713017242
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	913713017242
Net Weight (Piece)	2.019 kg

HID-Basic ballasts for HPL and HPI(PLUS) lamps

Dimensional drawing



Product

BHLE 250L 200 TS

BHLA 250 L200 TS

