



HF-Performer III for TL-D lamps

HF-P 258 TL-D III 220-240V 50/60Hz IDC

HF-Performer III TL-D III ballasts offer maximum versatility and meet all of the necessary commercial grade specifications. They also offer the added benefits of lamp striation reduction technology, making these ballasts compatible with energy-saving lamps. As such, these ballasts are part of an overall high-efficiency lighting system that may help you or your customers to achieve any international or local energy code you need to comply with. HF-Performer III TL-D III ballasts are the ideal choice for a broad range of new construction and retrofit applications within the commercial sector, including general surface mounting or office lighting, parking garages, warehouses, waterproof and other applications. The ballast is primarily designed for Indoor application. For outdoor application, the luminaire should be minimum Classland need to be sufficiently protected against water & dust. The installation should also be guard against any lightening surge or any other necessary electrical protection as deemed in such typical installation & application.

Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Inrush Current Width	0.35 ms
Power Factor (Fraction)	0.99
Inrush Current Peak (Max)	28 A
Number of Products on MCB (16A Type	12
B) (Nom)	

Wiring	
Connector Type Input Terminals	WAGO 251 universal connector [Suitable for
	both automatic wiring (ALF and ADS) and
	manual wiring]
Connector Type Output Terminals	WAGO 251 universal connector [Suitable for
	both automatic wiring (ALF and ADS) and
	manual wiring]
Temperature	
Ambient temperature range	-25 °C to 60 °C
T-Case Lifetime (Nom)	80 ℃


Datasheet, 2024, March 21 data subject to change

HF-Performer III for TL-D lamps

T-Case Maximum (Max)	80 ℃				
Mechanical and Housing					
Housing	L 280x30x28				
Approval and Application					
Ingress protection code	IP20 [Finger-protected]				
Energy Efficiency Index	A2 BAT				
Safety Standard	IEC 61347-2-3				
Environmental Standard	ISO 14001				
Approval Marks	CE marking ENEC certificate VDE-EMV				
	certificate				

Product Data					
Order product name	HF-P 258 TL-D III 220-240V 50/60Hz IDC				
Full product name	HF-P 258 TL-D III 220-240V 50/60Hz IDC				
Full product code	872790091172500				
Order code	913713031966				
Material Nr. (12NC)	913713031966				
Numerator - Quantity Per Pack	1				
EAN/UPC - Product/Case	8711500999726				
Numerator - Packs per outer box	12				
EAN/UPC - Case	8727900911725				

Dimensional drawing



Product	D1	C1	A1	A2	B1
HF-P 258 TL-D III 220-240V	4.2 mm	28.0 mm	280.0 mm	265.0 mm	30.0 mm
50/60Hz IDC					

