

Lighting

PHILIPS

HF-Selectalume II for TL5 lamps

HF-S 254 TL5 II 220-240V 50/60Hz

HF-Selectalume II TL5 is the most cost-effective, reliable and outstanding solution for fluorescent lamps. These ballasts are part of an overall high-efficiency lighting system that may help you or your customers to achieve any international or local energy code you need to comply with. HF-Selectalume II TL5 ballasts are the ideal choice for a broad range of new construction and retrofit applications within the commercial sector, including general surface mounting or office lighting, parking garages, warehouses, waterproof and other applications. The ballast is primarily designed for Indoor application. For outdoor application, the luminaire should be minimum Classland need to be sufficiently protected against water & dust. The installation should also be guard against any lightening surge or any other necessary electrical protection as deemed in such typical installation & application.

Product data

Operating and Electrical			
Input Voltage	220 to 240 V		
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		
Earth Leakage Current (Max)	0.5 mA		
Inrush Current Width	0.38 ms		
Inrush Current Peak (Max)	28 A		
Wiring			
Connector Type Input Terminals	WAGO 744 connector		
Connector Type Output Terminal	s WAGO 744 connector [Suitable for manual wiring]		
Temperature			
Ambient temperature range	-15 °C to 50 °C		


T-Case Lifetime (Nom)	75 °C
T-Case Maximum (Max)	75 °C
Mechanical and Housing	
Housing	L 280x30x21
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Energy Efficiency Index	A2 BAT
Approval Marks	F-Marking CE marking ENEC certificate CCC
	certificate C-Tick certificate PSB certification TISI
	marking SIRIM approval CB Certificate CCC certificate
	VDE-EMV certificate


HF-Selectalume II for TL5 lamps

Product Data	
Order product name	HF-S 254 TL5 II 220-240V 50/60Hz
Full product name	HF-S 254 TL5 II 220-240V 50/60Hz
Full product code	872790090562500
Order code	913713033766
Material Nr. (12NC)	913713033766

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500999382
Numerator - Packs per outer box	12
EAN/UPC - Case	8727900905625

Dimensional drawing





Product	D1	C1	A1	A2	B1
HF-S 254 TL5 II 220-240V 50/60Hz	4.1 mm	21.5 mm	360.0 mm	350.0 mm	30.0 mm



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2024, March 21 - data subject to change