



EB-Certalume for TL5 lamps

EB-C 114 TL5 220-240V 50/60Hz


Affordable, reliable, high frequency electronic ballast for TL5 fluorescent lamps, ideal alternative for electromagnetic (EM) ballasts

Product data

| Operating and Electrical | | Approval and Application | |
|---------------------------------|---|---------------------------------|--------------------------------|
| Input Voltage | 220 to 240 V | Ingress protection code | IP20 [Finger-protected] |
| Line Frequency | 50 to 60 Hz | Energy Efficiency Index | A2 |
| Input Frequency | 50 to 60 Hz | Approval Marks | CCC certificate CB Certificate |
| Earth Leakage Current (Max) | 0.7 mA | | |
| Wiring | | Product Data | |
| Connector Type Input Terminals | 250 manual connector [Suitable for manual wiring and easy release button] | Order product name | EB-C 114 TL5 220-240V 50/60Hz |
| Color Input Terminals | Orange | Full product name | EB-C 114 TL5 220-240V 50/60Hz |
| Color Output Terminals | Grey | Full product code | 872790088654200 |
| Connector Type Output Terminals | 250 manual connector [Suitable for manual wiring and easy release button] | Order code | 88654200 |
| | | Material Nr. (12NC) | 913713196214 |
| | | Numerator - Quantity Per Pack | 1 |
| | | EAN/UPC - Product/Case | 8711500998903 |
| | | Numerator - Packs per outer box | 50 |
| | | EAN/UPC - Case | 8727900886542 |
| Temperature | | | |
| T-Case Lifetime (Nom) | 75 °C | | |
| Mechanical and Housing | | | |
| Housing | L 275x20x21 | | |

EB-Certalume for TL5 lamps

Dimensional drawing



| Product | D1 | C1 | A1 | A2 | B1 |
|-------------------------------|--------|---------|----------|----------|---------|
| EB-C 114 TL5 220-240V 50/60Hz | 4.2 mm | 21.0 mm | 275.0 mm | 265.0 mm | 19.8 mm |

