



EB-Certalume for TL5 lamps

EB-C 114 TL5 220-240V 50/60Hz

Affordable, reliable, high frequency electronic ballast for TL5 fluorescent lamps, ideal alternative for electromagnetic (EM) ballasts


Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Earth Leakage Current (Max)	0.7 mA
Wiring	
Connector Type Input Terminals	250 manual connector [Suitable for manual wiring and easy release button]
Color Input Terminals	Orange
Color Output Terminals	Grey
Connector Type Output Terminals	250 manual connector [Suitable for manual wiring and easy release button]
Temperature	
T-Case Lifetime (Nom)	75 °C
Mechanical and Housing	
Housing	L 275x20x21

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Energy Efficiency Index	A2
Approval Marks	CCC certificate CB Certificate
Product Data	
Order product name	EB-C 114 TL5 220-240V 50/60Hz
Full product name	EB-C 114 TL5 220-240V 50/60Hz
Full product code	872790088654200
Order code	913713196214
Material Nr. (12NC)	913713196214
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500998903
Numerator - Packs per outer box	50
EAN/UPC - Case	8727900886542

EB-Certalume for TL5 lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
EB-C 114 TL5 220-240V 50/60Hz	4.2 mm	21.0 mm	275.0 mm	265.0 mm	19.8 mm

