



EB-Certalume for PLT/C lamps

EB-C 118 PL-T/C 220-240V 50/60Hz

Affordable, reliable, high frequency electronic ballast for 4-pin PL-T and PL-C fluorescent lamps, ideal alternative for electromagnetic (EM) ballasts


Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Number of Products on MCB (16A Type B) (Nom)	20
Wiring	
Connector Type Input Terminals	250 manual connector [Suitable for manual wiring and easy release button]
Color Input Terminals	Orange
Color Output Terminals	Grey
Connector Type Output Terminals	250 manual connector [Suitable for manual wiring and easy release button]
Temperature	
T-Case Lifetime (Nom)	65 °C
T-Case Maximum (Max)	65 °C
Mechanical and Housing	
Housing	- [Not Specified]

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Energy Efficiency Index	A2
Approval Marks	CCC certificate CB Certificate
Product Data	
Order product name	EB-C 118 PL-T/C 220-240V 50/60Hz
Full product name	EB-C 118 PL-T/C 220-240V 50/60Hz
Full product code	872790083288400
Order code	913713198614
Material Nr. (12NC)	913713198614
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500997746
Numerator - Packs per outer box	24
EAN/UPC - Case	8727900832884

EB-Certalume for PLT/C lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
EB-C 118 PL-T/C 220-240V 50/60Hz	4.2 mm	31.0 mm	94.0 mm	86.0 mm	72.0 mm

