



EB-Certalume for TL-D lamps

EB-C 236 TL-D 220-240V 50/60Hz

EB-Certalume is the most cost-effective, slim and affordable ballast for reliable operation of a fluorescent lamp. It is also the ideal entry-level product for electromagnetic system users who want to enjoy the benefits offered by electronic ballasts. The cost-saving and reliable EB-Certalume has energy efficiency class A2, and its robust design meets all relevant international safety and performance standards. EB-Certalume is intended for use with indoor lighting fixtures such as recessed luminaires, which are widely used in office, industrial, hotel, restaurant and other applications.

Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Number of Products on MCB (16A Type B) (Nom)	28
Wiring	
Connector Type Input Terminals	250 manual connector [Suitable for manual wiring and easy release button]
Color Input Terminals	Orange
Color Output Terminals	Grey
Connector Type Output Terminals	250 manual connector [Suitable for manual wiring and easy release button]


Temperature	
T-Case Lifetime (Nom)	75 °C
Mechanical and Housing	
Housing	L 210x40x30
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Energy Efficiency Index	A2
Approval Marks	CCC certificate CB Certificate
Product Data	
Order product name	EB-C 236 TL-D 220-240V 50/60Hz
Full product name	EB-C 236 TL-D 220-240V 50/60Hz
Full product code	872790085880800
Order code	913713199315
Material Nr. (12NC)	913713199315

EB-Certalume for TL-D lamps

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500998163
Numerator - Packs per outer box	20

EAN/UPC - Case	8727900858808
----------------	---------------

Dimensional drawing



Product	D1	C1	A1	A2	B1
EB-C 236 TL-D 220-240V 50/60Hz	4.2 mm	30.0 mm	210.0 mm	200.0 mm	40.0 mm

