

HID-Basic Semi-Parallel Economic ballasts for SON/CDM/MH lamps

BSNE 250L 301I TS

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.


Product data

Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking
Product Data	
Order product name	BSNE 250L 301I TS

Full product name	BSNE 250L 301I TS
Full product code	871829112578500
Order code	913713202650
Material Nr. (12NC)	913713202650
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291125785
Numerator - Packs per outer box	6
EAN/UPC - Case	8718291125792

HID-Basic Semi-Parallel Economic ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	C1	A1	B1
BSNE 250L 3011 TS	64.5 mm	159.0 mm	72.5 mm

