

SunStay

BRP710 Spare CC 2K Lm AIO

Integrated solar street light with Lithium Ferro Phosphate battery, solar panel and charger built into the luminaire. Pressure die cast aluminium for sturdiness and long life. Specially designed pole mounting bracket allows different tilt angles, lateral and pole top mounting.

Product data

General Information	
Driver included	Yes
CE mark	CE mark

Light Technical	
Luminous Efficacy (rated) (Nom)	175 lm/W

Operating and Electrical	
Battery type	Lithium Ferro Phosphate
Battery voltage	12.8 V
Charge controller type	MPPT
Charge controller wattage	11 W
Cable connection kit	Excluded

Temperature	
Ambient temperature range	0 to +35 °C

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Overall length	110 mm
Overall width	38 mm
Overall height	48 mm
Dimensions (Height x Width x Depth)	48 x 38 x 110 mm
Material	Acrylonitrile-butadiene-styrene

Application Conditions	
Solar dimming profile	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
Grid connection type	Off grid

Product Data	
Order product name	BRP710 Spare CC 2K Lm AIO
Full product name	BRP710 Spare CC 2K Lm AIO
Full product code	871016335633499
Order code	919415811075
Material Nr. (12NC)	919415811075
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163356334
Numerator - Packs per outer box	10
EAN/UPC - Case	8710163356655

SunStay

Dimensional drawing



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.