



# Greenled I 189/190/191/192/193/ 194/195 downlight

## DN192B LED9S-4000 PSU WH S1

GreenLed I family is general purpose High performance Led downlight family suitable for use in a series of lighting applications in Office, Retail and General Area Lighting . Available in a wide variety of lumen packs & color temp.

### Warnings and Safety

- Meant for use in Indoor environment only

### Product data

Light Technical		Controls and Dimming	
Correlated Color Temperature (Nom)	4000 K	Dimmable	No
Color rendering index (CRI)	>80	Control interface	-
Light source color	840 neutral white		
Luminaire light beam spread	110°		
Operating and Electrical		Mechanical and Housing	
Input Voltage	220-240 V	Housing Material	Aluminum die cast
Line Frequency	50 Hz	Housing Color	White
Input Frequency	50 Hz	Overall height	85 mm
Power Consumption	10 W	Overall diameter	150 mm
Power Factor (Fraction)	0.9	Material	Aluminum
Temperature		Approval and Application	
Ambient temperature range	0 to +45 °C	Ingress protection code	IP20 [Finger-protected]
		Mech. impact protection code	IK02 [0.2 J standard]
		Surge Protection (Common/Differential)	2.5 kV

Greenled I 189/190/191/192/193/194/195 downlight

Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Power consumption tolerance	+/-10%
Product Data	
Order product name	DN192B LED9S-4000 PSU WH S1

Full product name	DN192B LED9S-4000 PSU WH S1
Order code	919515810379
Material Nr. (12NC)	919515810379
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	8

Dimensional drawing

Product: GreenLED I  
Type: DN189B/ DN 190B/ DN 191B/ DN 192B/ DN193B/ DN 194B/ DN195B  
Application: Indoor

