



GreenPerform DN391/392/393/394/ 395 downlight

DN 392B LED 10S-3000 PSD WH

GreenPerform is a high performance Led downlight family suitable for use in a series of Lighting applications in Office, Retail and General Area Lighting. Available in a wide variety of lumen packs, color temp and options of all type of dimming(Phase Cut/Analogue/DALI), GreenPerform becomes the perfect solution for downlight applications for professional users.

Warnings and Safety

- Meant for use in Indoor environment only

Product data

General Information		Optical cover type		Polycarbonate
Driver included	Yes	Luminaire light beam spread		120°
Light source engine type	LED			
Warranty period	3 years	Operating and Electrical		
Flammability mark	For mounting on normally flammable surfaces	Input Voltage		220-240 V
		Line Frequency		50 Hz
		Power Consumption		10.6 W
		Power Factor (Fraction)		0.9
Light Technical		Temperature		
Luminous Flux	1,000 lm	Ambient temperature range		0 to +45 °C
Correlated Color Temperature (Nom)	3000 K			
Luminous Efficacy (rated) (Nom)	100 lm/W	Controls and Dimming		
Color rendering index (CRI)	>80	Dimmable		Yes
Beam angle of light source	120 degree(s)			
Light source color	830 warm white			
Optic type	-			

GreenPerform DN391/392/393/394/395 downlight

Control interface	DALI
Mechanical and Housing	
Housing Material	Aluminum Alloy
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	White
Mounting device	Spring clip for recess mounting
Overall height	70 mm
Overall diameter	150 mm
Material	Aluminum
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Surge Protection (Common/Differential)	2.5 kV
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Median useful life L70B50	40,000 hour(s)
Product Data	
Order product name	DN 392B LED 10S-3000 PSD WH
Full product name	DN 392B LED 10S-3000 PSD WH
Order code	919515810471
Material Nr. (12NC)	919515810471
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	8

Dimensional drawing

Product: GNI
Type: DN391B / DN392B / DN393B / DN394B/ DN395B
Application: Indoor

