



GreenPerform DN391/392/393/394/ 395 downlight

DN 392B LED10S-3000 PSU WH

GreenPerform is a high performance Led downlight family suitable for use in a series of Lighting applications in Office, Retail and General Area Lighting. Available in a wide variety of lumen packs, color temp and options of all type of dimming(Phase Cut/Analogue/DALI), GreenPerform becomes the perfect solution for downlight applications for professional users.

Warnings and Safety

- Meant for use in Indoor environment only

Product data

General Information	
Driver included	Yes
Light source engine type	LED
Warranty period	3 years
Flammability mark	For mounting on normally flammable surfaces
Light Technical	
Luminous Flux	1,000 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	120 degree(s)
Light source color	830 warm white
Optic type	-

Optical cover type	Polycarbonate
Luminaire light beam spread	120°
Operating and Electrical	
Input Voltage	220–240 V
Line Frequency	50 Hz
Power Consumption	10.6 W
Power Factor (Fraction)	0.9
Temperature	
Ambient temperature range	0 to +45 °C
Controls and Dimming	
Dimmable	No

GreenPerform DN391/392/393/394/395 downlight

Control interface	-
Mechanical and Housing	
Housing Material	Aluminum Alloy
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	White
Mounting device	Spring clip for recess mounting
Overall height	70 mm
Overall diameter	150 mm
Material	Aluminum
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Surge Protection (Common/Differential)	2.5 kV
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Median useful life L70B50	40,000 hour(s)
Product Data	
Order product name	DN 392B LED10S-3000 PSU WH
Full product name	DN 392B LED10S-3000 PSU WH
Order code	919515810489
Material Nr. (12NC)	919515810489
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	8

Dimensional drawing

Product: GNI
Type: DN391B / DN392B / DN393B / DN394B/ DN395B
Application: Indoor

