



Greenbay BY400V

BY400V LED110S CW AK PSU S2 FG LILO WH X

GreenBay is an integrally designed, versatile lighting solution from Philips to address lighting application requirements within industrial spaces. From under canopies to truss mounted medium bay luminaires, GreenBay can be used in variety of recessed , surface or suspended mounted applications.

Product data

General Information		Temperature	
Driver included	Yes	Ambient temperature range	0 to +45 °C
Light source engine type	LED	Controls and Dimming	
Warranty period	3 years	Dimmable	No
Flammability mark	For mounting on normally flammable surfaces	Control interface	-
Light Technical		Mechanical and Housing	
Luminous Flux	11,000 lm	Housing Material	Aluminum Alloy
Correlated Color Temperature (Nom)	5700 K	Optic material	Glass
Luminous Efficacy (rated) (Nom)	105 lm/W	Optical cover material	Polycarbonate
Color rendering index (CRI)	>70	Housing Color	White
Beam angle of light source	35 degree(s)	Mounting device	Via U Shaped Bracket, Aiming Scale Angle, Universal Installation
Light source color	756 cool white	Overall length	475 mm
Optic type	Double asymmetric optic 35°	Overall width	365 mm
Optical cover type	Glass	Overall height	165 mm
Luminaire light beam spread	35°	Dimensions (Height x Width x Depth)	165 x 365 x 475 mm
Operating and Electrical		Material	Aluminum
Input Voltage	240 V	Approval and Application	
Line Frequency	50 Hz	Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Power Consumption	110 W	Mech. impact protection code	IK07 [2 J reinforced]
Power Factor (Fraction)	0.9		

Greenbay BY400V

Surge Protection (Common/Differential)		Surge protection level until 4 kV
Protection class IEC	Safety class I	
Initial Performance (IEC Compliant)		
Power consumption tolerance	+/-10%	
Over Time Performance (IEC Compliant)		
Median useful life L70B50	50,000 hour(s)	

Product Data	
Order product name	BY400V LED110S CW AK PSU S2 FG LILO WH X
Full product name	BY400V LED110S CW AK PSU S2 FG LILO WH X
Order code	919515811062
Material Nr. (12NC)	919515811062
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

Product: GreenBay
Type: BY400V
Application: Indoor

