



# **SunStay**

# BRP710 LED20 CW MR S1 12V 35MO PDIM50 So

Integrated solar street light with Lithium Ferro Phosphate battery, solar panel and charger built into the luminaire. Pressure die cast aluminium for sturdiness and long life. Specially designed pole mounting bracket allows different tilt angles, lateral and pole top mounting.

### **Product data**

General Information	
Driver included	Yes
Light Technical	
Luminous Flux	2,000 lm
Correlated Color Temperature (Nom)	5700 K
Luminous Efficacy (rated) (Nom)	175 lm/W
Color rendering index (CRI)	>70
Light source color	Cool white
Optical cover type	UV stabilized Polycarbonate cover
Operating and Electrical	
Battery type	Lithium Ferro Phosphate
Battery ampere hour	13.6 Ah
Battery voltage	12.8 V
Battery charging & discharging cycles	2000
Panel type	Mono crystalline
Panel voltage	17 Vmp, 21 Voc V
Panel peak wattage	35 W
Charge controller type	MPPT

Temperature		
Ambient temperature range	0 to +35 °C	
Controls and Dimming		
Dimmable	Yes	
Configurability	Factory Configurable	
Mechanical and Housing		
Housing Material	Aluminium pressure die cast	
Housing Color	Gray	
Overall length	684 mm	
Overall width	369 mm	
Overall height	156 mm	
Dimensions (Height x Width x Depth)	156 x 369 x 684 mm	
Approval and Application		
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]	
Over Time Performance (IEC Compliant)		
Median useful life L70B50	50,000 hour(s)	
Application Conditions		
Ambient temperature range for charging	0 °C to +45 °C °C	


Datasheet, 2023, April 15 data subject to change

# **SunStay**

Ambient temperature range for	-20 °C to +35 °C °C
discharging (when light is on)	
Solar dimming profile	50% Dusk to dawn, 100% on Motion. ( Sensor
	disabled for 5 Hrs, after 5 Hrs)
Grid connection type	Off grid
Battery location	Inside Luminaire
Product Data	
Order product name	BRP710 LED20 CW MR S1 12V 35MO PDIM50
	So
Full product name	BRP710 LED20 CW MR S1 12V 35MO PDIM50
	So

Full product code	871951450180500
Order code	919515812626
Material Nr. (12NC)	919515812626
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514501805
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514501805

# Dimensional drawing





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.