



# GreenPerform Sleek

## DN295B LED6S-4000 PSU WH

Green Perform Sleek luminaire is designed for low dept false ceiling. Slim design with non-integral driver enables installation into low height false ceilings of different thickness and materials. Narrow rim semi-deep recessed design gives high quality lighting for designer ceilings. Highly efficient Electronic driver with high performance LED's ensures the longer life & high performance in this product category. Wide range of CCT's & Lumen packs suitable for various application.

### Warnings and Safety

- Meant for Indoor Application Only. Should not be used in outdoor environment.

### Product data

General Information		Operating and Electrical	
Driver included	Yes	Input Voltage	130-320 V
Light source engine type	LED	Line Frequency	50 Hz
Warranty period	2 years	Power Consumption	5.5 W
Flammability mark	For mounting on normally flammable surfaces	Power Factor (Fraction)	0.95
Light Technical		Temperature	
Luminous Flux	600 lm	Ambient temperature range	0 to +45 °C
Correlated Color Temperature (Nom)	4000 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	110 lm/W	Dimmable	No
Color rendering index (CRI)	>80	Control interface	-
Beam angle of light source	120 degree(s)	Mechanical and Housing	
Light source color	840 neutral white	Housing Material	Aluminum die cast
Optic type	Beam angle 120°	Optic material	Polycarbonate
Optical cover type	Polycarbonate	Optical cover material	Polycarbonate
Luminaire light beam spread	120°	Housing Color	White and black

GreenPerform Sleek

Mounting device	Spring clip for recess mounting
Material	Aluminum

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Surge Protection (Common/Differential)	Surge protection level until 2.5 kV
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Initial chromaticity	<5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Median useful life L70B50	50,000 hour(s)

Product Data

Order product name	DN295B LED6S-4000 PSU WH
Full product name	DN295B LED6S-4000 PSU WH
Order code	919515812846
Material Nr. (12NC)	919515812846
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20

Dimensional drawing

Product: GreenPerform Sleek  
Type: DN295/IDK296  
Application: Indoor Industrial

