PHILIPS

Lighting



GreenPerform Sleek

DN295B LED10S-3000 PSU WH

Green Perform Sleek luminaire is designed for low dept false ceiling. Slim design with non-integral driver enables installation into low height false ceilings of different thickness and materials. Narrow rim semi-deep recessed design gives high quality lighting for designer ceilings. Highly efficient Electronic driver with high performance LED's ensures the longer life & high performance in this product category. Wide range of CCT's & Lumen packs suitable for various application.

Warnings and Safety

• Meant for Indoor Application Only. Should not be used in outdoor environment.

Product data

General Information	
Driver included	Yes
Light source engine type	LED
Warranty period	2 years
Flammability mark	For mounting on normally flammable surfaces

Light Technical	
Luminous Flux	1,000 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	110 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	120 degree(s)
Light source color	830 warm white
Optic type	Beam angle 120°
Optical cover type	Polycarbonate
Luminaire light beam spread	120°

Operating and Electrical	
Input Voltage	130-320 V
Line Frequency	50 Hz
Power Consumption	9 W
Power Factor (Fraction)	0.95

Temperature	
Ambient temperature range	0 to +45 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Housing Material	Aluminum die cast
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	White and black
Mounting device	Spring clip for recess mounting

GreenPerform Sleek

Material	Aluminum

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Surge Protection (Common/Differential)	Surge protection level until 2.5 kV
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Initial chromaticity	<5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)


Median useful life L70B50	50,000 hour(s)


Product Data

Order product name	DN295B LED10S-3000 PSU WH
Full product name	DN295B LED10S-3000 PSU WH
Order code	919515812851
Material Nr. (12NC)	919515812851
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20

Dimensional drawing







© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.