



Standard Extra Low Voltage A60

STAN ELV 60W E27/BRC 50V A60 CL 1CT

Clear lamp (A-bulb) for operation on voltages of 24 and 50V

Product data

General Information	
Cap base	E27 [E27]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 h
Switching Cycle	4,000
Rated Lifetime (Hours)	1,000 h
Lighting Technology	Incandescent

Light Technical	
Luminous Flux	810 lm
Correlated Colour Temperature	2700 K
Colour rendering index (CRI)	100

Operating and Electrical	
Power Consumption	60.0 W
Starting time (nom.)	0.0 s
Warm-up time to 60% light	Instant full light s
Voltage (nom.)	50 V
Voltage (nom.)	50 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	A60 [A 60 mm]

Approval and Application	
Energy consumption kWh/1,000 hours	60 kWh

Product Data	
Order product name	Stan ELV 60W E27/BRC 50V A60 CL 1CT
Full product name	STAN ELV 60W E27/BRC 50V A60 CL 1CT
Full EOC	871150010188484
Order code	10188484
Material no. (12 NC)	920021025303
Local order code	5060ESCP
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500101884
Numerator – packs per outer box	120
EAN/UPC - Case	8711500348999

Standard Extra Low Voltage A60

Dimensional drawing



Product	D (max)	C (max)
Stan ELV 60W E27/BRC 50V A60 CL 1CT	60 mm	107.5 mm

