



Standard A-shape clear

Stan 40W E27 220-240V A55 CL 1CT/5X10F

Conventional pear-shaped incandescent lamps

Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	415 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A55 [A 55mm]
Product Data	
Order product name	Stan 40W E27 220-240V A55 CL 1CT/5X10F
Full product name	Stan 40W E27 220-240V A55 CL 1CT/5X10F
Full product code	871829112387300
Order code	920053843301
Material Nr. (12NC)	920053843301
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500011367
Numerator - Packs per outer box	50
EAN/UPC - Case	8718291123897

Standard A-shape clear

Dimensional drawing



Product	D (max)	D	C (max)
Stan 40W E27 220-240V A55 CL 1CT/5X10F	56 mm	55 mm	97 mm

