



CLASSICTONE

Standard

CLAS 40W E27 220-240V A55 CL 1CT/10X10F

Conventional pear-shaped incandescent lamps


Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	415 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A55 [A 55mm]
Product Data	
Order product name	CLAS 40W E27 220-240V A55 CL 1CT/10X10F
Full product name	CLAS 40W E27 220-240V A55 CL 1CT/10X10F
Full product code	871150001136701
Order code	920053843329
Material Nr. (12NC)	920053843329
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500011367
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500234001

CLASSICTONE Standard

Dimensional drawing



Product	D (max)	D	C (max)
CLAS 40W E27 220-240V A55 CL 1CT/10X10F	56 mm	55 mm	97 mm

