



# CLASSICTONE Standard

## CLASSICTONE 40W E27 220-240V A55 CL 1CT/ 10X10F

Conventional pear-shaped incandescent lamps


### Product data

General Information	
Cap-Base	E27 [ E27]
Operating Position	UNIVERSAL [ Any or Universal (U)]
Nominal Lifetime (Nom)	1000 h
Light Technical	
Luminous Flux (Nom)	415 lm
Color Rendering Index (Nom)	100
Operating and Electrical	
Power (Rated) (Nom)	40 W
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear

Approval and Application	
Energy Efficiency Label (EEL)	E
Product Data	
Full product code	871150001136701
Order product name	CLASSICTONE 40W E27 220-240V A55 CL 1CT/10X10F
EAN/UPC - Product	8711500011367
Order code	920053843329
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	100
Material Nr. (12NC)	920053843329
Net Weight (Piece)	0.025 kg
ILCOS Code	IAA/C-40-220-E27-55

# CLASSICTONE Standard

## Dimensional drawing



Product	D (max)	D	C (max)
CLASSICTONE 40W E27 220-240V A55 CL 1CT/ 10X10F	56 mm	55 mm	97 mm

STD 40W E27 220-240V A55 CL

