



Standard A-shape frosted

Standard 60W B22 240V A55 FR 1CT/10X10F

Conventional pear-shaped incandescent lamps

Product data

General Information	
Cap base	B22 [B22]
Burning Position	UNIVERSAL [Any/Universal]
Nominal lifetime (nom.)	1000 h

Light Technical	
Lamp Luminous Flux 25°C EL (Nom)	700 lm
Colour Rendering Index,horiz (Nom)	100

Operating and Electrical	
Power (Rated) (Nom)	60 W
Voltage (Nom)	240 V

Controls and Dimming	
Dimmable	yes


Mechanical and Housing	
Bulb finish	Frosted

Approval and Application	
Energy efficiency label (EEL)	E

Product Data	
Full product code	871829174630000
Order product name	Standard 60W B22 240V A55 FR 1CT/10X10F
EAN/UPC – product	8718291746300
Order code	74630000
Numerator – quantity per pack	1
Numerator – packs per outer box	100
Material no. (12NC)	920054445578
Net weight (piece)	35.000 g
ILCOS Code	IAA/F-60-240-B22d-55

Standard A-shape frosted

Dimensional drawing



Product

Standard 60W B22 240V A55 FR 1CT/10X10F

STD 60W B22 240V A55 FR

