



Standard A-shape frosted

Stan 60W B22 240V A55 FR 1CT/10X10F

Conventional pear-shaped incandescent lamps


Product data

General Information	
Cap-Base	B22 [B22]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	700 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	60 W
Voltage (Nom)	240 V
Voltage (Nom)	240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A55 [A 55mm]
Product Data	
Order product name	Stan 60W B22 240V A55 FR 1CT/10X10F
Full product name	Stan 60W B22 240V A55 FR 1CT/10X10F
Full product code	871829174630000
Order code	920054445578
Material Nr. (12NC)	920054445578
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291746300
Numerator - Packs per outer box	100
EAN/UPC - Case	8718291746324

Standard A-shape frosted

Dimensional drawing



Product	D	C (max)
Stan 60W B22 240V A55 FR 1CT/10X10F	55 mm	95.5 mm

