



CLASSICTONE Standard

CLAS 60W E27 220-240V A55 CL 1CT/10X10F

Conventional pear-shaped incandescent lamps

Product data

General Information	
Cap-Base	E27
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Luminous Flux	710 lm
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	60 W
Voltage (Nom)	220-240 V


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A55

Product Data	
Order product name	CLAS 60W E27 220-240V A55 CL 1CT/10X10F
Full product name	CLAS 60W E27 220-240V A55 CL 1CT/10X10F
Full product code	871150001138101
Order code	920054643329
Material Nr. (12NC)	920054643329
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500011381
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500234018

CLASSICTONE Standard

Dimensional drawing



Product	D (max)	D	C (max)
CLAS 60W E27 220-240V A55 CL 1CT/10X10F	56 mm	55 mm	97 mm

