



CLASSICTONE Standard

CLAS 60W E27 220-240V A55 CL 1CT/10X10F


Conventional pear-shaped incandescent lamps

Product data

Informasi Umum	
Tutup-Dasar	E27 [E27]
Posisi Pengoperasian	UNIVERSAL [Setiap atau Universal (U)]
Nominal masa pakai	1.000 jam
Teknologi Pencahayaan	Incandescent
Teknis Lampu	
Flux Cahaya	710 lm
Indeks renderasi warna (CRI)	100
Pengoperasian dan Kelistrikan	
Konsumsi Daya	60 W
Tegangan (Nom)	220-240 V
Kontrol dan Peredupan	
Dapat diredupkan	Ya

Mekanis dan Housing	
Lapisan bohlam	Bening
Bentuk Bohlam	A55 [A 55mm]
Data Produk	
Nama produk pesanan	CLAS 60W E27 220-240V A55 CL 1CT/10X10F
Nama lengkap produk	CLAS 60W E27 220-240V A55 CL 1CT/10X10F
Kode produk lengkap	871150001138101
Kode urutan	920054643329
No. Material (12NC)	920054643329
Numerator - Jumlah Per Pak	1
EAN/UPC - Produk/Kantung	8711500011381
Numerator - Pak per kotak bagian luar	100
EAN/UPC - Kantung	8711500234018

Dimensional drawing



Product	D (max)	D	C (max)
CLAS 60W E27 220-240V A55 CL 1CT/10X10F	56 mm	55 mm	97 mm

