



# Standard A-shape clear

## Standard 60W E27 240V A55 CL 1CT/10X10F


Conventional pear-shaped incandescent lamps

### Product data

General Information		Approval and Application	
Cap base	E27 [ E27]	Energy efficiency label (EEL)	E
Burning Position	UNIVERSAL [ Any/Universal]	<b>Product Data</b>	
Nominal lifetime (nom.)	1000 h	Full product code	871829174636200
<b>Light Technical</b>		Order product name	Standard 60W E27 240V A55 CL 1CT/10X10F
Lamp Luminous Flux 25°C EL (Nom)	700 lm	EAN/UPC – product	8718291746362
Colour Rendering Index,horiz (Nom)	100	Order code	74636200
<b>Operating and Electrical</b>		Numerator – quantity per pack	1
Power (Rated) (Nom)	60 W	Numerator – packs per outer box	100
Voltage (Nom)	240 V	Material no. (12NC)	920054645597
<b>Controls and Dimming</b>		Net weight (piece)	25.000 g
Dimmable	yes	ILCOS Code	IAA/C-60-240-E27-55
<b>Mechanical and Housing</b>			
Bulb finish	Clear		

## Standard A-shape clear

### Dimensional drawing



#### Product

Standard 60W E27 240V A55 CL 1CT/10X10F

STD 60W E27 240V A55 CL

