PHILIPS Lighting



Standard A-shape frosted

Stan 60W E27 120V A55 FR U 1CT/10X10F

Conventional pear-shaped incandescent lamps

Product data

General Information			
Cap-Base	E27 [E27]		
Operating Position	UNIVERSAL [Any or Universal (U)]		
Lighting Technology	Incandescent		
Light Technical			
Color rendering index (CRI)	100		
Operating and Electrical			
Power Consumption	60 W		
Voltage (Nom)	120 V		
Voltage (Nom)	120 V		
Controls and Dimming			
Dimmable	Yes		

Mechanical and Housing			
Bulb Finish	Frosted		
Bulb Shape	A55 [A 55mm]		
Product Data			
Order product name	Stan 60W E27 120V A55 FR U 1CT/10X10F		
Full product name	Stan 60W E27 120V A55 FR U 1CT/10X10F		
Full product code	871150007123101		
Order code	920054736379		
Material Nr. (12NC)	920054736379		
Numerator - Quantity Per Pack	1		
EAN/UPC - Product/Case	7702081004009		
Numerator - Packs per outer box	100		
EAN/UPC - Case	17702081004013		

Standard A-shape frosted

Dimensional drawing



Product	D (max)	D	C (max)
Stan 60W E27 120V A55 FR U 1CT/10X10F	56 mm	55 mm	97 mm



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, December 19 - data subject to change