



# Standard A-shape frosted

## Standard 100W B22 240V A55 FR 1CT/10X10F

Conventional pear-shaped incandescent lamps

### Product data

General Information	
Cap base	B22 [ B22]
Burning Position	UNIVERSAL [ Any/Universal]
Nominal lifetime (nom.)	1000 h

Light Technical	
Lamp Luminous Flux 25°C EL (Nom)	1330 lm
Colour Rendering Index,horiz (Nom)	100

Operating and Electrical	
Power (Rated) (Nom)	100 W
Voltage (Nom)	240 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb finish	Frosted

Product Data	
Full product code	871829174684300
Order product name	Standard 100W B22 240V A55 FR 1CT/10X10F
EAN/UPC – product	8718291746843
Order code	74684300
Numerator – quantity per pack	1
Numerator – packs per outer box	100
Material no. (12NC)	920056945581
Net weight (piece)	35.000 g
ILCOS Code	IAA/F-100-240-B22d-55

## Standard A-shape frosted

### Dimensional drawing



#### Product

Standard 100W B22 240V A55 FR 1CT/10X10F

STD 100W B22 240V A55 FR

