



CLASSICTONE Superlux

CLAS 40W E27 220-240V E50 W-W 1CT/10X10F

Mushroom-shaped (E-shaped) lamps in various diameters


Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	400 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	White window
Bulb Shape	E50 [E 50mm]
Product Data	
Order product name	CLAS 40W E27 220-240V E50 W-W 1CT/10X10F
Full product name	CLAS 40W E27 220-240V E50 W-W 1CT/10X10F
Full product code	871150022629700
Order code	920226243329
Material Nr. (12NC)	920226243329
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500226297
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500239679

CLASSICTONE Superlux

Dimensional drawing



Product	D	C (max)
CLAS 40W E27 220-240V E50 W-W 1CT/10X10F	50 mm	91 mm

