



# CLASSICTONE Superlux

CLAS 40W E27 220-240V E50 W-W 1CT/10X10F

Mushroom-shaped (E-shaped) lamps in various diameters

## Product data

Informasi Umum	
Tutup-Dasar	E27 [E27]
Posisi Pengoperasian	UNIVERSAL [Setiap atau Universal (U)]
Nominal masa pakai	1.000 jam
Teknologi Pencahayaan	Incandescent

Teknis Lampu	
Flux Cahaya	400 lm
Indeks renderasi warna (CRI)	100

Pengoperasian dan Kelistrikan	
Konsumsi Daya	40 W
Tegangan (Nom)	220-240 V

Kontrol dan Peredupan	
Dapat diredupkan	Ya


Mekanis dan Housing	
Lapisan bohlam	Jendela putih
Bentuk Bohlam	E50 [E 50mm]

Data Produk	
Nama produk pesanan	CLAS 40W E27 220-240V E50 W-W 1CT/10X10F
Nama lengkap produk	CLAS 40W E27 220-240V E50 W-W 1CT/10X10F
Kode produk lengkap	871150022629700
Kode urutan	920226243329
No. Material (12NC)	920226243329
Numerator - Jumlah Per Pak	1
EAN/UPC - Produk/Kantung	8711500226297
Numerator - Pak per kotak bagian luar	100
EAN/UPC - Kantung	8711500239679

# CLASSICTONE Superlux

## Dimensional drawing



Product	D	C (max)
CLAS 40W E27 220-240V E50 W-W 1CT/10X10F	50 mm	91 mm

