



Sign

20T6-1/2/IF 120V 24PK

Philips Sign bulbs provide the perfect light for dramatic accents and display lighting that is great for hard to reach signs, indoors and out.


Product data

General Information	
Cap-Base	E17 [Intermediate Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	150 lm
Operating and Electrical	
Power Consumption	20 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Frosted

Bulb Shape	T-6 1/2
Product Data	
Order product name	20T6-1/2/IF 120V 24PK
Full product name	20T6-1/2/IF 120V 24PK
Order code	920603636301
Material Nr. (12NC)	920603636301
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677248536
Numerator - Packs per outer box	24
EAN/UPC - Case	50046677248531

Sign

Dimensional drawing



Product

20T6-1/2/IF 120V 24PK

