



Reflector Flood

65BR/FL60 120V 24/1

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These flood lamps produce homogeneous beams of high intensity for general illumination.


Product data

| General Information | |
|--------------------------|---|
| Cap-Base | E26 [Single Contact Medium Screw] |
| Operating Position | H90 [Hanging +/-90D or Base Up HOR (BUH)] |
| Rated Lifetime (Hours) | 2,000 hour(s) |
| Lighting Technology | Incandescent |
| Light Technical | |
| Beam Angle (Nom) | 60 degree(s) |
| Luminous Flux | 620 lm |
| Operating and Electrical | |
| Power Consumption | 65 W |
| Voltage (Nom) | 120 V |
| Voltage (Nom) | 120 V |

| Mechanical and Housing | |
|---------------------------------|---------------------|
| Bulb Finish | Frosted |
| Bulb Shape | BR40 |
| Product Data | |
| Order product name | 65BR/FL60 120V 24/1 |
| Full product name | 65BR/FL60 120V 24/1 |
| Order code | 389130 |
| Material Nr. (12NC) | 920670036324 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677225360 |
| Numerator - Packs per outer box | 24 |
| EAN/UPC - Case | 50046677389135 |

Reflector Flood

Dimensional drawing



Product

65BR/FL60 120V 24/1

