



# Reflector Flood

## 65BR30/FL55 CDA 130V

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These flood lamps produce homogeneous beams of high intensity for general illumination.


### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	55 degree(s)
Luminous Flux	605 lumen
Operating and Electrical	
Power Consumption	65 W
Voltage (Nom)	130 V
Voltage (Nom)	130 V

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	BR30
Product Data	
Order product name	65BR30/FL55 CDA 130V
Order code	920681036112
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	920681036112
Full product name	65BR30/FL55 CDA 130V
EAN/UPC - Case	50046677225204
EAN/UPC - Product/Case	046677225209

# Reflector Flood

## Dimensional drawing



### Product

65BR30/FL55 CDA 130V

