



Reflector Flood

65BR30/FLVALUE PACK 1/12

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These flood lamps produce homogeneous beams of high intensity for general illumination.


Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	55 degree(s)
Luminous Flux	620 lm
Operating and Electrical	
Power Consumption	65 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	BR30
Product Data	
Order product name	65BR30/FLVALUE PACK 1/12
Full product name	65BR30/FLVALUE PACK 1/12
Order code	248872
Material Nr. (12NC)	920681036368
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677225827
Numerator - Packs per outer box	1
EAN/UPC - Case	50046677225822

Reflector Flood

Dimensional drawing



Product

65BR30/FLVALUE PACK 1/12

