



# Reflector Agro

## 75BR30/ARGO CDA 120V 6/1 TP

Philips Family of Reflector Agro provide the perfect light to promote plant growth.


### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	55 degree(s)
Luminous Flux	700 lm
Operating and Electrical	
Power Consumption	75 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Agro Blue

Bulb Shape	BR30
Approval and Application	
Approval Marks	Circle E logo
Product Data	
Order product name	75BR30/ARGO CDA 120V 6/1 TP
Full product name	75BR30/ARGO CDA 120V 6/1 TP
Order code	415281
Material Nr. (12NC)	920682436307
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677415280
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677415285

## Reflector Agro

### Dimensional drawing



#### Product

75BR30/ARGO CDA 120V 6/1 TP

