



# Standard Lustre P45 frosted

## Stan 25W E14 220-240V P45 FR 1CT/5X10F

Spherical vacuum- or gas-filled incandescent lamps with white or inside-frosted glass bulb and E- or B-base

### Product data

General Information	
Cap-Base	E14 [E14]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Luminous Flux	210 lm
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	25 W
Voltage (Nom)	220-240 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	P45 [P 45mm]

Product Data	
Order product name	Stan 25W E14 220-240V P45 FR 1CT/5X10F
Full product name	Stan 25W E14 220-240V P45 FR 1CT/5X10F
Full product code	871829112399600
Order code	921411143301
Material Nr. (12NC)	921411143301
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500223470
Numerator - Packs per outer box	50
EAN/UPC - Case	8718291124016

## Standard Lustre P45 frosted

### Dimensional drawing



Product	D	C (max)
Stan 25W E14 220-240V P45 FR 1CT/5X10F	45 mm	78 mm

